

The Filling Station

SAVE MONEY - IMPROVE ACCURACY

FEATURES

- Patented design.
- Most EMP jar sizes can be quickly interchanged.
- Optimizes the closed EMP system; less batch transfers and minimal storage costs.
- Works with right or left handed operators via switchable operating lever.
- Balanced actuation arm for easy operation.
- Made of durable stainless and powder coated steel for years of operation.
- Easy to clean and wipe down.
- Contrast background to help assure quality filling in see-through containers.
- Stabilizer plate for use when filling adapter type dispensers with EMP jars.
- Includes NEW nozzle specific for filling Topi-CLICK.

“Get ready - you will never think about topical filling the same way again.”



HOW IT WORKS:

- Uses tuned leverage to help push any size EMP jar plungers.
- Simple operation provides efficient use of existing pharmacy materials to keep costs of system and materials lower.

BENEFITS REPORTED BY EARLY ADOPTERS



- “Cuts filling time by at least 50%” for most batches.
- “...a lot less packing and tapping.” (helps eliminate air bubbles)
- “Less messy than other filling method.”
- “Has paid for itself.” (low cost compared to other fillers)
- “...anyone can be trained quickly.”
- “...less taxing on personnel.”
- “Fills more than just Topi-CLICK.”
- “We don’t have to fill 200g EMP jars 5 times over and over.”
- “Found more uses for it than filling.”
- “Reduced transfer time and less storage containers.”
- “More precise loading and filling.”

At only \$2,100 the Topi-CLICK Filling Station pays for itself very quickly. To order call 877.870.8448 or email info@doselogix.com.

